Clickeze [®] EZE-Swap[™] Cubicle Curtain

Snap Panel System



- Standard fabric or disposable panels are 66"x 66", but are also available in custom sizes
- Continuous Mesh Panels are made to order to meet your specific project's needs
- Panels overlap to provide full privacy
- Easily snap curtain panels off of mesh without the use of a ladder
- Curtains have been tested and pass fire safety standards

IPC.622/REV.7



Clickeze[®] EZE[™] Swap[™] Cubicle Curtain Snap Panel System

Suggested Specifications

PART 1 - GENERAL

1.01 SUMMARY

- A. Privacy Curtain
- 1.02 SECTION INCLUDES
- A. EZE•Swap[™] Cubicle Curtain Snap Panel System 1.03 REFERENCES
- 1.05 REFERENCES
- A. National Fire Protection Association (NFPA) 1.04 SYSTEM DESCRIPTION
- A. Performance Requirements: Provide privacy curtains that conform to the following requirements of regulatory agencies and the quality control of
- Clickeze, Inpro Corporation. 1. Fire Performance Characteristics: Provide curtains that conform with NFPA 701, Fire Tests for Flame and Resistant Textiles and Films.
- 1.05 SUBMITTALS
- A. Product Data: Manufacturer's printed product data for each type of privacy curtain specified.
- B. Fabric Samples: Swatch cards of fabric samples illustrating fabric color and weave.
- C. Manufacturer's Care Instruction: Printed care instructions for each curtain.
- 1.06 DELIVERY, STORAGE AND HANDLING
- A. Deliver materials in unopened factory packaging to the jobsite.
- B. Inspect materials at delivery to assure that specified products have been received.
- C. Store in original packaging in a climate controlled location away from direct sunlight.
- 1.07 PROJECT CONDITIONS
- A. Environmental Requirements: Products must be installed in an interior climate controlled environment.
- 1.08 WARRANTY
- A. Standard Clickeze [®] Limited Warranty against material and manufacturing defects.

PART 2 – PRODUCTS

2.01 MANUFACTURER

- A. Acceptable Manufacturer Clickeze, Inpro Corporation, PO Box 406 Muskego, WI 53150 USA; Telephone: 800.222.5556, Fax: 888.715.8407,
- Internet address: www.Inprocorp.com
- B. Substitutions: Not permitted
- C. Provide all privacy curtains from a single source.
- 2.02 MATERIALS
- A. Privacy Curtain
- Fabric: Provide 100% polyester curtains. Fabric is to be opaque, washable, flame retardant and closely woven.
- Shield Fabric: Provide 100% polyester, impregnated and multi-coated with Aqueous based microporous polymers.

- Sustainable Fabrics: Provide fabrics that contain Recycled Polyester or are made from 100% Eco Polyester. Eco polyester fabrics shall be free of chlorine and PBT's (persistent, bioaccumulative and/ or toxic substances).
- 4. Disposable Privacy Curtain Fabric: 100% Non-woven polypropylene with a thickness of 100 GSM.
- 5. Open Mesh Cloth: Provide curtain heading of open weave nylon mesh material with #50, 1/2" (12.7mm) holes (greater than 70% open) to permit air and steam circulation. Mesh is to be flame retardant, washable and dry-cleanable.
- 6. Grommets: Provide 4-ounce (113.4g) #2 nickelplated grommets that are machined into top mesh hem or mesh header placed six (6") inches on center.
- 7. Curtain Snaps:
- Bottom Mesh Footer: Provide rustproof, nickelplated brass snaps with off-white plastic cover spaced 4.6"(117mm) on center and machined into bottom mesh footer.
- b. Top Curtain Header: Provide rustproof, nickel-plated brass, double-sided snaps spaced 4.6"(117mm) on center and machined into top curtain header.
 2.03 FINISH AND COLOR
- A. Cubicle Privacy Fabric: Select solid or patterned
- fabric from manufacturer's standard selection.
- B. Open Mesh Cloth: Provide curtain heading of mesh material in a color selected from manufacturer's standard selection.
- 2.04 FABRICATION
- A. Fabricate curtains to comply with the following requirements:
- Horizontal Width: Provide finished panel width of 66" horizontal, custom widths available upon request. Panel to be manufactured with 1-¼" double turned hems on hree (3) sides. Snap panels shall have a single turned 1-1/2" top hem. Along top horizontal width, double-sided snaps made of nickel-plated brass to be machined into fabric and set at 4.6"(117mm) on center.
- 2. Vertical Length: Provide finished panel vertical length of 66", custom lengths available upon request.
- a. Bottom of privacy curtains hang 12"-15" (304.8-355.6mm) above finished floor. Height tolerance \pm 2.0".
- 3. Mesh: Mesh to be manufactured in one horizontal continuous piece sized to be 10% wider than the track length but no less than 12" (304.8mm) extra fullness. Width tolerance \pm 3". Mesh height will vary to accommodate specific application or needs.
- a. Bottom mesh hem to be single-turned and reinforced with webbed tape stitched with double needle lock stitch no less than 1-1/4" in width.

- b. Side mesh hems to be double turned and stitched with double needle lock stitch no less than 1-1/4" in width.
- c. Sewing Options
- 1. Framing: Self curtain fabric sewn on all four (4) sides of mesh.
- 2. Top Banding: Self curtain fabric sewn at mesh header (where grommets are placed).
- 3. Bottom Banding: Self curtain fabric sewn at mesh footer (where snaps are placed).

PART 3 – EXECUTION

- 3.01 EXAMINATION
- A. Examine areas and conditions in which the cubicle tracking systems will be installed.
- Complete all finishing operations, including painting, before beginning installation of cubicle tracking system materials.
- 2. Verify that surfaces and above ceiling supports are ready to receive work.
- 3.02 PREPARATION
- A. General: Prior to installation, clean substrate to remove dust, debris and loose particles.
- 3.03 INSTALLATION
- A. General: Locate the cubicle track as indicated on the approved detail drawing for the appropriate substrate and in compliance with the Clickeze * installation instructions.
- B. Installation of Cubicle Tracking Systems:
- 1. Install cubicle track, secure, rigid, and true to ceiling line.
- 2. Slide carriers onto the track.
- 3. Install end cap or stop device.
- 4. Secure or suspend track to ceiling system. Install with mechanical fasteners or Gridclips.
- 5. Install curtains on carriers ensuring smooth operation.
- EZE Swap Curtain Installation
- 1. Attach mesh to cubicle track carriers.
- 2. Snap curtain panels onto mesh from each end.
- 3. Overlap curtain panels at desired width for
- complete privacy then snap to the end of panel
- Disposable Panels Only Place adhesive disc at bottom of panel overlap for added privacy when using disposable fabric panels.
- 3.04 CLEANING
- A. At completion of the installation, remove any debris and clean surfaces in accordance with the Clickeze ° clean-up and maintenance instructions.

inpro.